Floraline Floralwall FD7 FD4 88"

The perfect end cap for your store. Constructed with display steps in the lower section and adjustable shelves on the back wall, you'll have plenty of options to show off your product. This is a refrigerated floral fixture at a classic height with full lighting.

Features:

•Soft Air Flow Environment - evenly distributed floral envelope, sealed with our air curtain to simulate a closed door case.

•Consistent low air temperature.

•High Humidity Environment.


•Polyurethane foamed in place insulation.


•Your choice of laminate and trim packages to match any color palette. •Mirrored slat wall option allows adjustably for your shelving and creates a dynamic display.


•Shelving options - Choose our unique powder coated convertible metal shelving and have the flexibility to merchandise buckets or arrangements. You may also select our elegant tempered glass shelf.

•Available as remote or self-contained refrigeration.











Drain Trap Supplied Loose (90 fitting to floor drain not included)


Floraline Display Products Corporation - www.floraline.com 38160 Western Parkway Willoughby, Ohio 44904 Phone: (440) 975-9449 or 800-239-3722 Fax: (440) 918-9043

Floraline Display Products Corporation - www.floraline.com 38160 Western Parkway Willoughby, Ohio 44904 Phone: (440) 975-9449 or 800-239-3722 Fax: (440) 918-9043

Disclaimer Notice: Product specifications, drawings, materials, construction methods, pricing and availability subject to change without notice.

Disclaimer Notice: Product specifications, drawings, materials, construction methods, pricing and availability subject to change without notice.





Refrigeration Stub Out

-Electric Stub Out

4 4 4 4 4 5			
1.1 AMP		FD4-88"	
0.5 AMP	115V	1PH	60Hz
2 times daily for 30 minutes each			
6,944	R-404A Standard		
2.2 AMP		FD7LCRC-88"	
1.1 AMP	115V	1PH	60Hz
2 times daily for 30 minutes each			
12,152	R-404A Standard		
	0.5 AMP 2 times dail 6,944 2.2 AMP 1.1 AMP 2 times dail	0.5 AMP 115V 2 times daily for 30 m 6,944 R-40 2.2 AMP 1.1 AMP 115V 2 times daily for 30 m	0.5 AMP115V1PH2 times daily for 30 minutes ea6,944R-404A Standa2.2 AMPFD7I1.1 AMP115V1PH2 times daily for 30 minutes ea